

**Indexable insert for turning SCMT 09T308, for finish machining****Order data**

Order number	260744 HB7010-2
GTIN	4069515020848
Item class	21G

Technical description

Cutting depth a_p	0.2 - 1.5 mm
Cutting conditions	continuous
Number of changes/inserts	4
Corner radius	0.8 mm
Main application	P
Cutting speed v_c main application	150 - 500 m/min
Finishing/roughing assignment	Finishing
Feed f	0.07 - 0.25 mm/rev.
Chip breaker	SS
ISO code indexable insert	SCMT 09T308
Tool material	Carbide

Type	HB7010-2
Type of product	Indexable insert for turning