

Garant**Indexable insert for turning VB.T 110304, for medium machining****Order data**

Order number	261224 HB7020-2
GTIN	4069515022118
Item class	21G

Technical description

Cutting speed v_c main application	110 - 350 m/min
ISO code indexable insert	VBMT 110304
Tolerance	M
Number of changes/inserts	2
Main application	P
Cutting conditions	slightly interrupted
Tool material	Carbide
Feed f	0.08 - 0.3 mm/rev.
Cutting depth a_p	0.3 - 2 mm
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing

Data sheet

Chip breaker	SM
Type	HB7020-2
Type of product	Indexable insert for turning