

Garant**Indexable insert for turning TNMG 160408, for finish machining****Order data**

Order number	251434 HB7010-2
GTIN	4069515017886
Item class	21G

Technical description

Finishing/roughing assignment	Finishing
Number of changes/inserts	6
ISO code indexable insert	TNMG 160408
Type	HB7010-2
Tool material	Carbide
Chip breaker	SS
Main application	P
Cutting depth a_p	0.3 - 2 mm
Corner radius	0.8 mm
Feed f	0.1 - 0.4 mm/rev.
Cutting speed v_c main application	170 - 500 m/min
Cutting conditions	continuous

Type of product

Indexable insert for turning