

Garant**Indexable insert for turning DNMG 150604, for medium machining****Order data**

Order number	250760 HB7010-2
GTIN	4069515017046
Item class	21G

Technical description

Tolerance	M
ISO code indexable insert	DNMG 150604
Tool material	Carbide
Type	HB7010-2
Cutting depth a_p	0.3 - 4 mm
Cutting conditions	continuous
Chip breaker	SM
Cutting speed v_c main application	140 - 440 m/min
Main application	P
Feed f	0.2 - 0.5 mm/rev.
Finishing/roughing assignment	Finishing

Data sheet

Number of changes/inserts	4
Corner radius	0.4 mm
Type of product	Indexable insert for turning