

Garant**Indexable insert for turning DNMG 150608, for roughing machining****Order data**

Order number	250862 HB7130-2
GTIN	4069515022804
Item class	21G

Technical description

Corner radius	0.8 mm
Cutting depth a_p	1.5 - 6 mm
Tool material	Carbide
Finishing/roughing assignment	Finishing
Main application	M
Feed f	0.25 - 0.6 mm/rev.
ISO code indexable insert	DNMG 150608
Number of changes/inserts	4
Type	HB7130-2
Cutting conditions	slightly interrupted
Cutting speed v_c main application	60 - 220 m/min

Chip breaker	VG
Type of product	Indexable insert for turning