

Garant**Indexable insert for turning CNMM 160612, for coarse machining****Order data**

Order number	250458 HB7020-2
GTIN	4069515016568
Item class	21G

Technical description

Cutting depth a_p	2 - 10 mm
Feed f	0.4 - 1.2 mm/rev.
Main application	P
Tool material	Carbide
ISO code indexable insert	CNMM 160612
Chip breaker	SR
Type	HB7020-2
Cutting speed v_c main application	140 - 300 m/min
Cutting conditions	slightly interrupted
Finishing/roughing assignment	Roughing
Corner radius	1.2 mm

Data sheet

Number of changes/inserts	4
Type of product	Indexable insert for turning