

Garant**Indexable insert for turning VNMG 160404, for medium machining****Order data**

Order number	251802 HB7010-2
GTIN	4069515018227
Item class	21G

Technical description

Cutting depth a_p	0.3 - 4 mm
Corner radius	0.4 mm
Type	HB7010-2
Chip breaker	SM
Tool material	Carbide
Finishing/roughing assignment	Finishing
Number of changes/inserts	4
Main application	P
Feed f	0.2 - 0.5 mm/rev.
ISO code indexable insert	VNMG 160404
Cutting speed v_c main application	140 - 440 m/min

Data sheet

Cutting conditions	continuous
Tolerance	M
Type of product	Indexable insert for turning