

Garant**Indexable insert for turning CNMG 160616, for roughing machining****Order data**

Order number	250338 HB7020-2
GTIN	4069515016483
Item class	21G

Technical description

Feed f	0.25 - 0.6 mm/rev.
Cutting speed v_c main application	110 - 360 m/min
Corner radius	1.6 mm
Main application	P
Finishing/roughing assignment	Roughing
ISO code indexable insert	CNMG 160616
Type	HB7020-2
Cutting depth a_p	1.5 - 6 mm
Chip breaker	SG
Tool material	Carbide
Number of changes/inserts	4

Data sheet

Cutting conditions

slightly interrupted

Type of product

Indexable insert for turning