

Garant**Indexable insert for turning VBMT 160404, for finish machining****Order data**

Order number	261152 HB7020-2
GTIN	4069515021999
Item class	21G

Technical description

Number of changes/inserts	2
Type	HB7020-2
ISO code indexable insert	VBMT 160404
Cutting depth a_p	0.2 - 1.5 mm
Cutting speed v_c main application	140 - 400 m/min
Feed f	0.07 - 0.25 mm/rev.
Cutting conditions	slightly interrupted
Chip breaker	SS
Tool material	Carbide
Finishing/roughing assignment	Finishing
Main application	P

Data sheet

Corner radius

0.4 mm

Type of product

Indexable insert for turning