

**Garant****Indexable insert for turning CC.T 09T302, for finish machining****Order data**

|              |                 |
|--------------|-----------------|
| Order number | 260056 HB7010-2 |
| GTIN         | 4069515019286   |
| Item class   | 21G             |

**Technical description**

|                                      |                     |
|--------------------------------------|---------------------|
| Type                                 | HB7010-2            |
| Feed f                               | 0.07 - 0.25 mm/rev. |
| Corner radius                        | 0.2 mm              |
| Main application                     | P                   |
| Cutting depth $a_p$                  | 0.2 - 1.5 mm        |
| Chip breaker                         | SS                  |
| Cutting speed $v_c$ main application | 150 - 500 m/min     |
| Number of changes/inserts            | 2                   |
| Finishing/roughing assignment        | Finishing           |
| Tolerance                            | M                   |
| Cutting conditions                   | continuous          |

## Data sheet

|                           |                              |
|---------------------------|------------------------------|
| ISO code indexable insert | CCMT 09T302                  |
| Tool material             | Carbide                      |
| Type of product           | Indexable insert for turning |