


Garant**Indexable insert for turning WNMG 080408, for medium machining****Order data**

Order number	252070 HB7020-2
GTIN	4069515018883
Item class	21G

Technical description

Cutting speed v_c main application	130 - 370 m/min
Cutting depth a_p	0.3 - 4 mm
ISO code indexable insert	WNMG 080408
Number of changes/inserts	6
Cutting conditions	slightly interrupted
Type	HB7020-2
Tolerance	M
Tool material	Carbide
Corner radius	0.8 mm
Finishing/roughing assignment	Finishing
Main application	P
Feed f	0.2 - 0.5 mm/rev.

Chip breaker	SM
Type of product	Indexable insert for turning