

Garant**Indexable insert for turning DC.T 11T302, for medium machining****Order data**

Order number	260458 HB7010-2
GTIN	4069515020565
Item class	21G

Technical description

Main application	P
Cutting depth a_p	0.3 - 2 mm
Tolerance	M
ISO code indexable insert	DCMT 11T302
Corner radius	0.2 mm
Number of changes/inserts	2
Type	HB7010-2
Feed f	0.08 - 0.3 mm/rev.
Cutting speed v_c main application	120 - 440 m/min
Cutting conditions	continuous
Finishing/roughing assignment	Finishing

Data sheet

Tool material	Carbide
Chip breaker	SM
Type of product	Indexable insert for turning