


**Indexable insert for turning WNMG 060408, for medium machining****Order data**

Order number	252064 HB7010-2
GTIN	4069515018722
Item class	21G

Technical description

Main application	P
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Cutting speed v_c main application	140 - 440 m/min
ISO code indexable insert	WNMG 060408
Tool material	Carbide
Chip breaker	SM
Number of changes/inserts	6
Cutting conditions	continuous
Tolerance	M
Cutting depth a_p	0.3 - 4 mm
Type	HB7010-2

Data sheet

Feed f	0.2 - 0.5 mm/rev.
Type of product	Indexable insert for turning