

Garant**Indexable insert for turning DC.T 11T308, for medium machining****Order data**

Order number	260464 HB7035-2
GTIN	4069515020725
Item class	21G

Technical description

Main application	P
ISO code indexable insert	DCMT 11T308
Type	HB7035-2
Tolerance	M
Cutting depth a_p	0.3 - 2 mm
Cutting speed v_c main application	80 - 290 m/min
Corner radius	0.8 mm
Cutting conditions	heavily interrupted
Tool material	Carbide
Number of changes/inserts	2
Chip breaker	SM

Data sheet

Feed f	0.08 - 0.3 mm/rev.
Finishing/roughing assignment	Finishing
Type of product	Indexable insert for turning