

Garant**Indexable insert for turning VB.T 160404, for medium machining****Order data**

Order number	261232 HB7010-2
GTIN	4069515022156
Item class	21G

Technical description

Type	HB7010-2
Cutting conditions	continuous
Tool material	Carbide
ISO code indexable insert	VBMT 160404
Finishing/roughing assignment	Finishing
Chip breaker	SM
Cutting depth a_p	0.3 - 2 mm
Corner radius	0.4 mm
Main application	P
Cutting speed v_c main application	120 - 440 m/min
Number of changes/inserts	2

Data sheet

Tolerance	M
Feed f	0.08 - 0.3 mm/rev.
Type of product	Indexable insert for turning