

Garant**Indexable insert for turning TNMG 160408, for medium machining, Wiper****Order data**

Order number	251545 HB7020-2
GTIN	4069515018081
Item class	21G

Technical description

Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
ISO code indexable insert	TNMG 160408
Tool material	Carbide
Number of changes/inserts	6
Chip breaker	WSM
Main application	P
Feed f	0.2 - 0.6 mm/rev.
Cutting conditions	slightly interrupted
Cutting speed v_c main application	140 - 420 m/min
Cutting depth a_p	0.5 - 4 mm
Type	HB7020-2

Type of product

Indexable insert for turning