

Garant**Indexable insert for turning VB.T 160404, for medium machining****Order data**

Order number	261232 HB7020-2
GTIN	4069515022170
Item class	21G

Technical description

Tolerance	M
Type	HB7020-2
Cutting conditions	slightly interrupted
Finishing/roughing assignment	Finishing
Cutting depth a_p	0.3 - 2 mm
Main application	P
Corner radius	0.4 mm
Chip breaker	SM
Cutting speed v_c main application	110 - 350 m/min
Feed f	0.08 - 0.3 mm/rev.
ISO code indexable insert	VBMT 160404

Data sheet

Tool material	Carbide
Number of changes/inserts	2
Type of product	Indexable insert for turning