

Garant**Indexable insert for turning VBMT 160408, for finish machining****Order data**

Order number	261154 HB7010-2
GTIN	4069515022033
Item class	21G

Technical description

Feed f	0.07 - 0.25 mm/rev.
Chip breaker	SS
Cutting conditions	continuous
Cutting depth a_p	0.2 - 1.5 mm
Tool material	Carbide
ISO code indexable insert	VBMT 160408
Main application	P
Number of changes/inserts	2
Finishing/roughing assignment	Finishing
Cutting speed v_c main application	150 - 500 m/min
Type	HB7010-2

Data sheet

Corner radius	0.8 mm
Type of product	Indexable insert for turning