

Garant**Indexable insert for turning VC.T 160408, for finish machining****Order data**

Order number	261374 HB7010-2
GTIN	4069515022514
Item class	21G

Technical description

Corner radius	0.8 mm
Tool material	Carbide
Feed f	0.07 - 0.25 mm/rev.
Cutting conditions	continuous
Cutting speed v_c main application	150 - 500 m/min
Main application	P
Type	HB7010-2
Tolerance	M
Finishing/roughing assignment	Finishing
ISO code indexable insert	VCMT 160408
Cutting depth a_p	0.2 - 1.5 mm

Data sheet

Number of changes/inserts	2
Chip breaker	SS
Type of product	Indexable insert for turning