



Pro Eco lever lock toolholder DDJNR 93°, for indexable inserts DD., right



Order data

Order number	250632 20/15
GTIN	4069515004022
Item class	22E

Description

Version:

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

Technical description

Lever screw	259019 2
Standard	Works standard
Shank size	20 mm
ISO code toolholder	PDJNR/L 2020K15
Lever	259016 1
Shim	259034 2
Functional width L ₄	32 mm
Head length L ₁	36 mm
suitable indexable insert	DN.. 1506..
Overall length L	125 mm
Insert size	15 mm
Pin	259045 1

Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	Facing
Type of product	Screw-on toolholder

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/250632-20/15>