


**Indexable insert for turning WNMG 060408, for medium machining****Order data**

Order number	252064 HB7035-2
GTIN	4069515018760
Item class	21G

Technical description

Finishing/roughing assignment	Finishing
Feed f	0.2 - 0.5 mm/rev.
Chip breaker	SM
Main application	P
Number of changes/inserts	6
Tolerance	M
ISO code indexable insert	WNMG 060408
Cutting speed v_c main application	120 - 320 m/min
Tool material	Carbide
Cutting depth a_p	0.3 - 4 mm
Corner radius	0.8 mm
Type	HB7035-2

Data sheet

Cutting conditions

heavily interrupted

Type of product

Indexable insert for turning