


**Indexable insert for turning WNMG 080408, for roughing machining****Order data**

Order number	252208 HB7130-2
GTIN	4069515022866
Item class	21G

Technical description

Cutting depth a_p	1.5 - 6 mm
Type	HB7130-2
Number of changes/inserts	6
Cutting conditions	slightly interrupted
Finishing/roughing assignment	Roughing
ISO code indexable insert	WNMG 080408
Feed f	0.25 - 0.6 mm/rev.
Chip breaker	VG
Main application	M
Tool material	Carbide
Cutting speed v_c main application	60 - 220 m/min
Corner radius	0.8 mm

Type of product

Indexable insert for turning