



## Pro Eco lever lock toolholder PCLNL 95°, for indexable inserts PC.., left



### Order data

|              |               |
|--------------|---------------|
| Order number | 250045 20/12  |
| GTIN         | 4069515004060 |
| Item class   | 22E           |

### Description

#### Version:

Targeted cooling on the cutting edge.

#### Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

### Technical description

|                                 |                 |
|---------------------------------|-----------------|
| Lever                           | 259016 1        |
| suitable indexable insert       | CN.. 1204..     |
| Head length L <sub>1</sub>      | 26 mm           |
| Overall length L                | 125 mm          |
| Shim                            | 259034 1        |
| ISO code toolholder             | PCLNR/L 2020K12 |
| Functional width L <sub>4</sub> | 31 mm           |
| Shank size                      | 20 mm           |
| Insert size                     | 12 mm           |
| Standard                        | Works standard  |
| Series                          | Pro Eco         |
| Lever screw                     | 259019 1        |

|                        |                               |
|------------------------|-------------------------------|
| Pin                    | 259045 1                      |
| Application type       | left-hand                     |
| Through-coolant        | yes                           |
| Setting angle $\kappa$ | 95 degrees                    |
| Application            | External longitudinal turning |
| Application            | Facing                        |
| Type of product        | Screw-on toolholder           |

### Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/250045-20/12>