

Garant**Indexable insert for turning VC.T 110304, for finish machining****Order data**

Order number	261366 HB7010-2
GTIN	4069515022330
Item class	21G

Technical description

Cutting conditions	continuous
Cutting speed v_c main application	150 - 500 m/min
Chip breaker	SS
Tool material	Carbide
Tolerance	M
Number of changes/inserts	2
Finishing/roughing assignment	Finishing
Corner radius	0.4 mm
Cutting depth a_p	0.2 - 1.5 mm
Main application	P
Type	HB7010-2

Data sheet

Feed f	0.07 - 0.25 mm/rev.
ISO code indexable insert	VCMT 110304
Type of product	Indexable insert for turning