



Pro Eco lever lock toolholder DDJNL 93°, for indexable inserts DD.., left



Order data

Order number	250633 25/15
GTIN	4069515004091
Item class	22E

Description

Version:

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

Technical description

Lever screw	259019 2
Head length L ₁	36 mm
Shim	259034 2
Insert size	15 mm
Shank size	25 mm
Overall length L	150 mm
Standard	Works standard
Lever	259016 1
ISO code toolholder	PDJNR/L 2525M15
suitable indexable insert	DN.. 1506..
Functional width L ₄	32 mm
Pin	259045 1

Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	Facing
Type of product	Screw-on toolholder

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/250633-25/15>