

**Indexable insert for turning TCMT 16T308, for medium machining****Order data**

Order number	260988 HB7010-2
GTIN	4069515021739
Item class	21G

Technical description

Cutting depth a_p	0.3 - 2 mm
Feed f	0.08 - 0.3 mm/rev.
Type	HB7010-2
Corner radius	0.8 mm
Chip breaker	SM
Cutting conditions	continuous
ISO code indexable insert	TCMT 16T308
Cutting speed v_c main application	120 - 440 m/min
Main application	P
Tool material	Carbide
Tolerance	M
Number of changes/inserts	3

Data sheet

Finishing/roughing assignment

Finishing

Type of product

Indexable insert for turning