

Garant**Indexable insert for turning VB.T 160404, for medium machining****Order data**

Order number	261232 HB7035-2
GTIN	4069515022194
Item class	21G

Technical description

Feed f	0.08 - 0.3 mm/rev.
Tolerance	M
Corner radius	0.4 mm
Number of changes/inserts	2
ISO code indexable insert	VBMT 160404
Cutting depth a_p	0.3 - 2 mm
Tool material	Carbide
Cutting speed v_c main application	80 - 290 m/min
Chip breaker	SM
Cutting conditions	heavily interrupted
Finishing/roughing assignment	Finishing

Data sheet

Type	HB7035-2
Main application	P
Type of product	Indexable insert for turning