



BMT longitudinal toolholder, BMT: WT150



Order data

Order number	319885 WT150
GTIN	4069515004282
Item class	32U

Description

Version:

High-precision arbors adapted to the specific machine, for flexible use on main and counter-spindle machines. Contact face and functional face ground. Perfectly matched for the respective lathe.

Suitable for conventional toolholders.

Advantage:

- **Design optimised for weight and geometry.**
- **Process reliability thanks to high-quality materials, long working life.**
- **Burnished for better corrosion protection.**
- **With secured ball spray nozzles up to 80 bar.**

Application:

Internal and external machining in CNC lathes with BMT tool turrets.

Mainly for external machining.

Suitable for:

CNC lathes with BMT tool turret.

- **Nakamura-Tome: NA55A, WT-150, WT-150 II, WT-250 II, WT-150 II (Capto Turret), WT-250, WTS-150, WTW-150, TW-10, TW-20 (16 ST), SC-150, SC-200, SC-200 II (12 ST), SC-250, Super NTJ, Super NTJX, Super NTM³, AS-200 (12 ST), AS-200 (15 ST), JX-200, 250, NTY³-150(V), 250, WY-150(V), 250**

- **CMZ:** TTL / TX 52, 66, TA 15, 20, 25, 30 M/MS/Y/YS (15 ST), TA Z400, 640, 1100 (15 ST), TD 15-55 M/MS/Y/YS (15 ST)
- **Muratec:** MT 1065EX (12×))
- **Eurotech:** TA 15, 20, 25, 30 M/MS/Y/YS (15 ST), TD 15-55 M/MS/Y/YS (15 ST), TTL / TX 52, 66
- **Accuway:** UA-200 Y, UA-330 LY, UA-1500 T2Y2, UA-1500 T2Y

Note:

Other BMT holders with different sizes and dimensions are available on request.
Please note that you must check the compatibility of the holder with your machine before purchasing. We cannot guarantee that it will fit correctly.

Technical description

h ₁	20 mm
L ₂	60 mm
L ₁	50 mm
h ₂	80 mm
b ₂	40 mm
x	65 mm
Type of product	Steel toolholder