


Garant**Master Eco clamping toolholder short SVHCR 107.5°, for indexable inserts SV.., right****Order data**

Order number	261298 25/16
GTIN	4069515004565
Item class	21U

Description**Version:**

Highly efficient cooling directly on the cutting edge and additional flank face cooling.

Note:

Coolant transfer via slot on the underside of the shank in conjunction with GARANT Master Eco holders No. 319006 – 319136 or No. 317900 for shank length < 125 mm. Optional connection possibility via hose connection (G 1/8 inch) No. 269207 and 269208.

Technical description

Overall length L	110 mm
ISO code toolholder	SVHCR/L 2525X16
Standard	Works standard
Series	Master Eco
Shank size	25 mm
Insert size	16 mm
Head length L ₁	40 mm
Functional width L ₄	32 mm
Set of insert screws	269023 3
suitable indexable insert	VC.. 1604..

Shim screw	269013 7
Shim	259033 5
Application type	right-hand
Through-coolant	yes
Setting angle κ	107.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Suitable products

No Shop URL available for: 261298 25/16