

Garant**Indexable insert for turning CNMG 160608, for medium machining****Order data**

Order number	250168 HB7010-2
GTIN	4069515016049
Item class	21G

Technical description

Type	HB7010-2
Feed f	0.2 - 0.5 mm/rev.
Finishing/roughing assignment	Finishing
Tolerance	M
Cutting conditions	continuous
Corner radius	0.8 mm
Number of changes/inserts	4
ISO code indexable insert	CNMG 160608
Cutting depth a_p	0.3 - 4 mm
Cutting speed v_c main application	140 - 440 m/min
Chip breaker	SM

Data sheet

Main application	P
Tool material	Carbide
Type of product	Indexable insert for turning