

Garant**Indexable insert for turning WNMG 060408, for finish machining****Order data**

Order number	251954 HB7020-2
GTIN	4069515018449
Item class	21G

Technical description

Chip breaker	SS
Finishing/roughing assignment	Finishing
Corner radius	0.8 mm
Main application	P
Cutting depth a_p	0.3 - 2 mm
Feed f	0.1 - 0.4 mm/rev.
Number of changes/inserts	6
Type	HB7020-2
Cutting conditions	slightly interrupted
Cutting speed v_c main application	160 - 400 m/min
Tool material	Carbide
ISO code indexable insert	WNMG 060408

Type of product

Indexable insert for turning