



BMT boring bar holder, BMT: 65-100



Order data

Order number	319887 65-100
GTIN	4069515004688
Item class	32U

Description

Version:

High-precision arbors adapted to the specific machine, for flexible use on main and counter-spindle machines. Contact face and functional face ground. Perfectly matched for the respective lathe.

For internal and external cooling.

Advantage:

- **Design optimised for weight and geometry.**
- **Process reliability thanks to high-quality materials, long working life.**
- **Burnished for better corrosion protection.**
- **With secured ball injection nozzles up to 80 bar.**

Application:

Internal and external machining in CNC lathes with BMT tool turrets.

For internal machining with boring bar holder or indexable drills.

Suitable for:

CNC lathes with BMT tool turret.

- **DN SOLUTIONS (formerly DOOSAN): PUMA GT3100; PUMA 3100; SMX 2600; SMX 3100; PUMA 2100 II; PUMA 2600 II**
- **EMCO: Hyperturn 100 Powermill; Maxxturn 110**

- **GOODWAY:** GLS-2800; GLS-3300; GMS-2000; GS-2000; GS-2600; GS-2800; GS-3300; GS-3600; GMT-2000
- **HURCO:** TMX10; TMX8
- **HYUNDAI WIA:** L2000; L2600; L3000; L300; LV450; HD2600; HD3100; SKT250; SKT300
- **ROMI:** GL 350
- **SPINNER:** TC800
- **TAKISAWA TAIWAN:** LX-2500; LX-3000; NEX-110; NX-2500; NX-2500; LA-250
- **Tongtai:** TNL-120; TD-2000; TD-2500
- **VICTOR:** Vturn-A26; Vturn-S26; Vturn-A260
- **WELE:** HL-200
- **YCM:** BTX-250SY

Note:

Other BMT holders with different sizes and dimensions are available on request.
Please note that you must check the compatibility of the holder with your machine before purchasing. We cannot guarantee that it will fit correctly.

Technical description

X	100 mm
d _a	40 mm
L ₃	51 mm
L ₁	73 mm
Z	64 mm
l ₁	132 mm
h ₁	95 mm
L ₂	70 mm
Type of product	Steel toolholder