

Garant**Indexable insert for turning VC.T 160408, for finish machining****Order data**

Order number	261374 HB7020-2
GTIN	4069515022538
Item class	21G

Technical description

Feed f	0.07 - 0.25 mm/rev.
Corner radius	0.8 mm
Finishing/roughing assignment	Finishing
ISO code indexable insert	VCMT 160408
Number of changes/inserts	2
Cutting conditions	slightly interrupted
Tolerance	M
Chip breaker	SS
Cutting depth a_p	0.2 - 1.5 mm
Main application	P
Cutting speed v_c main application	140 - 400 m/min

Data sheet

Type	HB7020-2
Tool material	Carbide
Type of product	Indexable insert for turning