

**BMT boring bar holder, BMT: WT100-75****Order data**

Order number	319887 WT100-75
GTIN	4069515004701
Item class	32U

Description**Version:**

High-precision arbors adapted to the specific machine, for flexible use on main and counter-spindle machines. Contact face and functional face ground. Perfectly matched for the respective lathe.

For internal and external cooling.

Advantage:

- **Design optimised for weight and geometry.**
- **Process reliability thanks to high-quality materials, long working life.**
- **Burnished for better corrosion protection.**
- **With secured ball injection nozzles up to 80 bar.**

Application:

Internal and external machining in CNC lathes with BMT tool turrets.

For internal machining with boring bar holder or indexable drills.

Suitable for:

CNC lathes with BMT tool turret.

- **Nakamura-Tome: NA44A; WT-100; NTJ-100; NTY³-100(V), WY-100 II/V (12 ST); SC-100**
- **CMZ: TTS 38, 46, 52, 66 M/Y**
- **Muratec: MT 100, 1051, 1065 (15-Station)**
- **Genturn: C42MYS; CW42 MY**

- **Goodway: GTZ-1500Y**
- **Hasegawa: C25/42; CW42**

Note:

Other BMT holders with different sizes and dimensions are available on request.

Please note that you must check the compatibility of the holder with your machine before purchasing. We cannot guarantee that it will fit correctly.

Technical description

d _a	25 mm
Z	31 mm
l ₁	92 mm
h ₁	80 mm
x	75 mm
L ₂	40 mm
L ₃	31 mm
L ₁	55 mm
Type of product	Steel toolholder