

Garant**Indexable insert for turning VC.T 110304, for finish machining****Order data**

Order number	261366 HB7020-2
GTIN	4069515022354
Item class	21G

Technical description

Chip breaker	SS
Cutting depth a_p	0.2 - 1.5 mm
Tolerance	M
Main application	P
Type	HB7020-2
Cutting speed v_c main application	140 - 400 m/min
Corner radius	0.4 mm
Finishing/roughing assignment	Finishing
Number of changes/inserts	2
Cutting conditions	slightly interrupted
ISO code indexable insert	VCMT 110304

Data sheet

Feed f	0.07 - 0.25 mm/rev.
Tool material	Carbide
Type of product	Indexable insert for turning