



Clamping cam, Threads: M12



Order data

Order number	370052 M12
GTIN	4059245559718
Item class	37K

Description

Advantage:

- **Compact design.**
- **Quick and easy clamping of components.**

Application:

For lateral clamping of narrow and wide workpieces. The workpiece is clamped by tightening the fixture clamp with a spanner.

Material:

Heat treatable steel, burnished

Technical description

Clamping force	9.3 kN
Length L	17 mm
maximum tightening torque	90 Nm
Ø D	34 mm
L ₁	23.2 mm

Data sheet

Stroke S	6.2 mm
Height H ₂	18 mm
Height H ₁	12 mm
Height H	24 mm
Width across flats AF	27 mm
AF ₁	10 mm
Type of product	Side clamps