



Shrink-fit unit, Type: ISG1200



Order data

Order number	354405 ISG1200
GTIN	085144000000
Item class	35B

Description

Version:

- Easily enter shrink parameters by scanning barcodes.
- Energy-saving induction technology for a long tool life.
- Precise centering of the tool.
- Only a small amount of space required and suitable for mobile use.
- Very high holding force and lasting strength, even in oily environments.
- ThermoGrip® shrink-fit units have been synonymous with innovative premium shrinking equipment for over 20 years.
- Clamping range Ø 3 – 32 mm for all shrink-fit chucks T, TSF, TB (HSS Ø 6 - 16 mm / carbide Ø 3 - 32 mm).
- Integrated air cooling (cooling adapter available as an option).
- Maximum tool length for HSK-A63 450 mm.
- Ideal for workbenches.

Supplied with:

- 1 barcode scanner
- Magnetic strip set
- Shrink-fit chuck catalogue
- Safety gloves
- Screening plates

· Operating instructions

Optional extras:

Screening plates No. 354241, tool mounting No. 354225 – 354227.

Technical description

Power	6.5 kW
Power supply	400V / 16A / 50Hz
Height	767 mm
Width	315 mm
Cooling time	300 s
Weight	25 kg
Length	410 mm
Type of product	Shrink-fit unit

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/354405-ISG1200>
