



Centring clamp Form A, Thread × length: M8X25



Order data

Order number	370053 M8X25
GTIN	4059245267774
Item class	37K

Description

Version:

Form A with countersunk screw.

Advantage:

- **Pull-down effect.**
- **Quick and easy clamping of components.**

Application:

For centring and clamping a workpiece in the hole. High clamping forces are achieved by the wedge surfaces.

Material:

Heat treatable steel, burnished Hardened (33-39 HRC).

Note:

During the clamping process, the clamping force acts on specific points of the hole wall.

Technical description

D _{max}	22 mm
D _{min}	16 mm

Data sheet

H	11.5 mm
Width across flats AF	5 mm
H ₁	1.6 mm
L	16.2 mm
maximum clamping force	4 kN
Type of product	Jig clamping system