



## KOMET Reamax® TS holder DAH® Zero Plain shank, long, for reaming head Ø D: 27-34,99mm



### Order data

Order number	239940 27-34,99
GTIN	
Item class	27E

### Description

#### Version:

The holder is pre-loaded and set to < 0.005 mm run-out. For run-out accuracies to precision < 3 µm, longer tool life, and higher process reliability.

#### Suitable for:

Reaming heads No. 239805; 239811; 239816; 239822; 239826.

#### Supplied with:

Holder complete with pull stud, spanner for pull stud and activation key.  
Please order a hexagon key L-wrench separately if required.

### Technical description

Shank length $L_s$	56 mm
Overall length $L_{tot}$	236 mm
Wrench No. 239901	8AF
Pull stud No. 239900	4
for reaming head Ø D	27 - 34.99 mm
Overhang A	180 mm
Activation wrench No. 239902	3AF (5Nm)
Shank Ø $D_s$ h6	25 mm
Shank type	long
Through-coolant	yes
Type of product	Phillips bit

---

## Accessories

Pull stud Type 4	239900 4
Wrench for pull studs Drive SW8	239901 SW8