




Wedge clamp, narrow version smooth, Thread M x length L: M10X25mm



Order data

Order number	370026 M10X25
GTIN	4059245032709
Item class	37K

Description

Application:

- Wedge surfaces produce high clamping forces.
- Wedge clamps can be used in tapped holes or T-slots.
- When the clamping screw is screwed in, the clamping segments press against the workpieces.
- A slot in the double wedge allows for movement and tolerance adjustment. Movement distance: M8 = ± 0.5 mm; M10 and M12 = ± 1.0 mm; M16 = ± 1.5 mm.
- Wedge clamps are suitable for multiple clamping.

Material:

Double wedge and clamping segments heat-treatable steel, hardened, black.

Technical description

Length L	25 mm
Thread	M10
Width B	28 mm
Height E	3.5 mm

Data sheet

Height C	19 mm
A maximum	37 mm
A minimum	32 mm
maximum clamping force	20 kN
Type of product	Side clamps