



KOMET Reamax® TS holder DAH® Zero Plain shank, long, for reaming head Ø D: 35-41,99mm



Order data

Order number	239940 35-41,99
GTIN	4047109280076
Item class	27E

Description

Version:

The holder is pre-loaded and set to < 0.005 mm run-out. For run-out accuracies to precision < 3 µm, longer tool life, and higher process reliability.

Suitable for :

Reaming heads No. 239805; 239811; 239816; 239822; 239826.

Supplied with:

Holder complete with pull stud, spanner for pull stud and activation key.

Please order a hexagon key L-wrench separately if required.

Through-coolant: yes

Overhang A: 200 mm

Overall length L_{tot} : 256 mm

Shank length L_s : 56 mm

Shank Ø D_s h6: 25 mm

Pull stud No. 239900: 5

Wrench No. 239901: 10AF

Technical description

Shank length L_s	56 mm
Pull stud No. 239900	5
Activation wrench No. 239902	3AF (6Nm)
Overhang A	200 mm
for reaming head Ø D	35 - 41.99 mm
Overall length L_{tot}	256 mm

Wrench No. 239901	10AF
Shank \varnothing D _s h6	25 mm
Shank type	long
Through-coolant	yes
Type of product	Phillips bit

Accessories

Pull stud Type 5	239900 5
Wrench for pull studs Drive SW10	239901 SW10