



Knurl forming tool Sliding headstock lathe universal, Shank size: 10mm



Order data

Order number	290009 10
GTIN	
Item class	29H

Description

Version:

Grub screw in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

Modular design: Can be used universally as right-hand or left-hand version.

Technical description

for knurl $\varnothing d_1$	10 mm
for knurl width w	4 mm
Working range	3 - 25 mm
Roller pin	299910 5
for knurl bore $\varnothing d_2$	4 mm
Cutting direction	left-hand and right-hand
for knurl profile	RAA 2×AA
for knurl profile	RBL 2×BR
for knurl profile	RGE45° BL/BR45°
for knurl profile	RAA 1×AA
for knurl profile	RBR 2×BL
Type of product	Self-centring knurling tool

