



## Knurl forming tool Sliding headstock lathe universal, Shank size: 10mm



### Order data

|              |           |
|--------------|-----------|
| Order number | 290089 10 |
| GTIN         |           |
| Item class   | 29H       |

### Description

#### Version:

Grub screws in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

**Modular design: Can be used universally as right-hand or left-hand version.**

### Technical description

|                                           |                             |
|-------------------------------------------|-----------------------------|
| for knurled countersunk $\varnothing d_3$ | 11 mm                       |
| for knurl width w                         | 6 mm                        |
| Working range                             | 3 - 40 mm                   |
| for knurl bore $\varnothing d_2$          | 6 mm                        |
| for knurl $\varnothing d_1$               | 15 mm                       |
| Disc                                      | 299927 1                    |
| Closure stud                              | 299925 1                    |
| Cutting direction                         | left-hand and right-hand    |
| for knurl profile                         | RAA 2×AA                    |
| Type of product                           | Self-centring knurling tool |