



Cut knurling tool Sliding headstock lathe universal, Shank size: 10mm



Order data

Order number	290197 10
GTIN	
Item class	29H

Description

Version:

Modular design: Can be used universally as right-hand or left-hand version.

Carbide running sleeve for increased wear resistance.

Quick tool adjustment by using the adjustment spindle.

Grub screw in the shank for clearance angle correction.

Technical description

Carbide sleeve, cover disc, screw	299920 10
for knurl width w	3 mm
for knurl $\varnothing d_1$	10 mm
Working range	0 - 15 mm
for knurl bore $\varnothing d_2$	6 mm
Cutting direction	left-hand and right-hand
for knurl profile	RBR45° 1×BL15°
for knurl profile	RAA 1×BL30°
for knurl profile	RBR30° 1×AA
for knurl profile	RAA 1×BR30°
for knurl profile	RBL45° 1×BR15°
for knurl profile	RBL30° 1×AA

Type of product

Self-centring knurling tool