



Holder for diamond burnishing tips Swivelling head left, Shank size: 10-16



Order data

Order number	291407 10-16
--------------	--------------

GTIN	
------	--

Item class	29M
------------	-----

Description

Version:

Swivelling tool head (adjustment range $\pm 90^\circ$).

Advantage:

Surface quality $R_z < 1 \mu\text{m}$ possible.

Application:

For machining materials up to 65 HRC. Ideal for machining the surfaces of complex, continuous contours.

For burnishing of **uninterrupted contours** (convex, concave, cylindrical, conical) and flat faces. Suitable even for applications up to the collar.

Supplied with:

Shank size 10 including shank adaptor 12 mm $\times$ 12 mm and 16 mm $\times$ 16 mm.

Attention:

Diamond burnishing tips must be ordered separately!

Note:

For detailed application recommendations please see the instruction handbook supplied.

Technical description

Shank size	10-16 mm
------------	----------

Type of product

Smooth rolling tool