


**DNMG 150604, Grade: CA510**

**Order data**

Order number	250696 CA510
GTIN	4960664698455
Item class	25E

**Description**

DNMG 150604 CA510 Grade: CA510  
 Chip breaker: PQ  
 Cutting depth  $a_p$ : 0.2 - 2.5 mm  
 Feed  $f$ : 0.13 - 0.4 mm/rev.  
 Cutting speed  $v_c$  main application: 180 - 590 m/min

**Technical description**

Cutting depth $a_p$	0.2 - 2.5 mm
Cutting speed $v_c$ main application	180 - 590 m/min
Cutting conditions	continuous
Chip breaker	PQ
Main application	P
Feed $f$	0.13 - 0.4 mm/rev.
Corner radius	0.4 mm

Grade	CA510
Finishing/roughing assignment	Finishing
Tool material	Carbide
ISO code indexable insert	DNMG 150604
Number of changes/inserts	4
Type of product	Indexable insert for turning