



Burnishing roller, Tip radius: 0,4mm



Order data

Order number	291419 0,4
GTIN	4030741082481
Item class	29M

Description

Advantage:

Surface quality of up to Rz 2 µm possible.

Inexpensive alternative to diamond burnishing up to a surface quality of Rz < 2 µm.

Application:

For machining materials up to 45 HRC. Ideal for machining the surfaces of complex, continuous contours.

Note:

Use the largest possible radius.

For detailed application recommendations please see the instruction handbook supplied.

Technical description

Radius	0.4 mm
Type of product	Smooth rolling tool