



DNMG 150604, Grade: CA525

Order data

Order number	250696 CA525
GTIN	4960664681037
Item class	25E

Description

DNMG 150604 CA525 Grade: CA525

Chip breaker: PQ

Cutting depth a_p : 0.2 - 2.5 mm

Feed f : 0.13 - 0.4 mm/rev.

Cutting speed v_c main application: 105 - 435 m/min

Technical description

Indexable insert clearance angle	degrees
Product name attribute	
Insert assignment	
Rake	degrees
Shim	
Indexable insert profile	neutral
Type of product	