

Garant

Shrink-fit chuck with cooling channel bores, SK 50 short, Clamping range Ø D1: 32mm



Order data

Order number	302292 32
GTIN	4045197288578
Item class	31A

Description

Version:

- **High-temperature steel.**
- **Size 3 -5 for carbide, from size 6 for HSS and carbide.**
- **All shanks hard turned (for smooth running!).**
- **With RFID/Balluffchip bore.**

With **coolant hole bores** tapped for plugging.

Coolant hole bores at clamping Ø D1: 3, 4 and 5 mm cannot be plugged.

Application:

For clamping tools with parallel shank to h6 tolerance.

Suitable for inductive, contact, and hot-air shrink units.

Optional extras:

Pull studs (PS) No. 308600 – 308800. PS wrenches No. 308820 – 308835, Shrink-fit chuck extensions No. 302410 – 302419. Shrink-fit units, accessories No. 354210 – 354450, balancing screws set No. 309906 size 180.

Technical description

Overhang dimension A	100 mm
Clamping Ø D ₁	32 mm
Ø D ₂	44 mm
External Ø D	53 mm

Cooling channel bore	lockable
Adapter	SK 50 short
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 μm
Machining strategy	HSC
Machining strategy	HPC
Type of product	Shrink-fit chuck

Accessories

Pull studsealed suitable for steep tapers 50	308660 50
Special pull stud with internal thread suitable for steep tapers 50	308740 50
Pull stud, 18CrNiMo7Form A suitable for steep tapers 50	308605 50
Cooling unit Type CU1	354215 CU1
Pull stud 45°sealed suitable for steep tapers 50	308760 50
Pull stud 90°sealed suitable for steep tapers 50	308795 50
Pull studsealed, form B suitable for steep tapers 50	308650 50
Cooling adapter long4.5° for clamping Ø 22,1-32 mm	354236 22,1-32
Screening plate for coilSU1 for clamping Ø 20-32 mm	354240 20-32
Pull stud 90°sealed suitable for steep tapers 50	308790 50
Pull studForm B suitable for steep tapers 50	308640 50
Cooling adapter short4.5° for clamping Ø 22,1-32 mm	354235 22,1-32
Pull studsealed, form B suitable for steep tapers 50	308620 50
Basic tool mountingfor SK for SK taper shank 50	354225 50
Pull stud, 18CrNiMo7sealed, form B suitable for steep tapers 50	308615 50

Pull studForm A suitable for steep tapers 50	308600 50
Wrench for pull studsISO 7388 suitable for ISO taper size 50	308830 50
Shrink-fit unit Type SU1	354210 SU1
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 50	308820 50
Pull studsealed, form A suitable for steep tapers 50	308610 50
Pull stud 45°sealed suitable for steep tapers 50	308765 50
Pull stud 60°sealed suitable for steep tapers 50	308785 50
Special pull stud with no internal threadsealed suitable for steep tapers 50	308720 50