

**Holder M-Drill, Shank: MK2****Order data**

Order number	080750 MK2
GTIN	4069515008570
Item class	BAW

Description**Version:**

Very quickly produce core holes in thin-walled materials using frictional heat. Can be used on CNC, NC and pillar drilling machines.

The M-Drill collet chucks are equipped with an aluminium cooling ring with bores to efficiently dissipate the heat generated during flow drilling. As a result, no heat is introduced into the machine spindle.

Standard or long; with or without a collar.

Suitable for:

HOLEX ER collets No. 308964.

ER clamping wrench No. 309680 25.

HOLEX fluteless tap No. 139130 or No. 139180.

Technical description

Overhang dimension A	76 mm
External Ø D	42 mm
Clamping range	1 - 16 mm

Data sheet

ER chuck key	25
for ER collets	25
Spare ER clamping nut	25
Type of product	Collet chucks